

HS4YN24 Cut Sheet



GC Valves solenoid coil, 24 VAC, 10W, 18mm DIN style wiring plug. For use with S201, NS201, S301 and NS301 valves.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/HS4YN24>

Technical Specifications

| | |
|-----------------------|------------------------------------|
| Brand | GC Valves |
| Item | Solenoid coil |
| Replacement | No |
| Voltage Rating | 24 VAC |
| Power Rating | 10W |
| Electrical Connection | 18mm DIN style wiring plug |
| For Use With | S201, NS201, S301 and NS301 valves |

Agency Approvals

| | |
|----------------------|--|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | No |
| EU REACH | View EU REACH document |