

HSB-2BG Cut Sheet



NITRA air stand-alone base, aluminum alloy, 145 psi (10 bar) maximum operating pressure, G3/8 female BSPP inlet(s), G3/8 female BSPP outlet(s), G3/8 female BSPP exhaust(s), bottom orientation. For use with ISO 5599/1 size 2 solenoid valves.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/HSB-2BG>

Technical Specifications

Brand	NITRA
Item	Stand-alone base
Working Fluid	Air
Material	Aluminum alloy
Maximum Operating Pressure	145 psi (10 bar)
Inlet Port	G3/8 female BSPP
Outlet Port	G3/8 female BSPP
Exhaust Port	G3/8 female BSPP
Hole Orientation	Bottom
For Use With	ISO 5599/1 size 2 solenoid valves

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/HSB-2BG.pdf>
See store item page for other formats.