

HT-BP060A Cut Sheet



Metrol limit switch, high temperature, precision touch, 6mm diameter, threaded, 1mm pitch, 47.8mm length, 3mm head, ball plunger, 6-13N contact force, N.O. contact(s), 6.5ft/2m cable length, pigtail.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/HT-BP060A>

Technical Specifications

Brand	Metrol
Item	Limit switch
Application	High temperature
Switch Type	Precision touch
Diameter	6mm
Barrel Type	Threaded
Length	47.8mm
Head Type	3mm
Actuator Type	Ball plunger
Contact Force	6-13N
Contact Type	N.O.
Cable Length	6.5ft/2m
Connection	Pigtail
Conductor Size	24 AWG
Stroke	0.8mm
Repeatability	0.01mm
Thread Pitch	1mm
Material	Stainless steel
IP Rating	IP40
Operating Temperature	0 to 200 deg C
Includes	Mounting hardware

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document