

# HT-FL75 Cut Sheet



Cembre manual hydraulic driver, 360-degree adjustable head. (2) pullers (TD-11 and TD-19) and 0.45in spiral bit included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/HT-FL75>

---

## Technical Specifications

<b>Brand</b>	Cembre
<b>Item</b>	Manual hydraulic driver
<b>Replacement</b>	No
<b>Head Type</b>	360-degree adjustable
<b>Maximum Punch Diameter</b>	5.5in
<b>Operation Type</b>	Manual hand pump
<b>Application</b>	Hole cutting
<b>Pulling Force</b>	75 kN (16,860 lbf)
<b>Includes</b>	(2) pullers (TD-11 and TD-19) and 0.45in spiral bit
<b>Package Type</b>	Plastic case
<b>Additional Information</b>	Punches and dies sold separately

---

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>