

HT8GBCV7 Cut Sheet



Eaton pushbutton, 30mm, momentary, incandescent illuminated, operator only, metal base, metal bezel, Operator: clear, extended, 28mm, round, plastic, 120 VAC/VDC, full voltage.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/HT8GBCV7>

Technical Specifications

Brand	Eaton	Bezel Material	Metal
Item	Pushbutton	Operator Color	Clear
NEMA Rating	1/2/3/3R/4/4X/12/13	Operator Type	Extended
Barrel Size	30mm	Operator Size	28mm
Action	Momentary	Operator Shape	Round
Bulb Type	Incandescent illuminated	Operator Material	Plastic
Contact Type	Operator only	Voltage Rating	120 VAC/VDC
Base Material	Metal	Voltage Regulation	Full voltage

Agency Approvals

UL Listed File #	E131568
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	68551
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document