

HT8GBWV7 Cut Sheet



Eaton pushbutton, 30mm, momentary, incandescent illuminated, operator only, metal base, metal bezel, Operator: white, extended, 28mm, round, plastic, 120 VAC/VDC, full voltage.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/HT8GBWV7>

Technical Specifications

| | |
|---------------|--------------------------|
| Brand | Eaton |
| Item | Pushbutton |
| NEMA Rating | 1/2/3/3R/4/4X/12/13 |
| Barrel Size | 30mm |
| Action | Momentary |
| Bulb Type | Incandescent illuminated |
| Contact Type | Operator only |
| Base Material | Metal |

| | |
|--------------------|--------------|
| Bezel Material | Metal |
| Operator Color | White |
| Operator Type | Extended |
| Operator Size | 28mm |
| Operator Shape | Round |
| Operator Material | Plastic |
| Voltage Rating | 120 VAC/VDC |
| Voltage Regulation | Full voltage |

Agency Approvals

| | |
|----------------------|----------------------------------------|
| UL Listed File # | E131568 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | 68551 |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |