

# HT8GBYV3 Cut Sheet



Eaton pushbutton, 30mm, momentary, incandescent illuminated, operator only, metal base, metal bezel, Operator: yellow, extended, 28mm, round, plastic, 24 VAC/VDC, full voltage.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/HT8GBYV3>

## Technical Specifications

|                      |                          |
|----------------------|--------------------------|
| <b>Brand</b>         | Eaton                    |
| <b>Item</b>          | Pushbutton               |
| <b>NEMA Rating</b>   | 1/2/3/3R/4/4X/12/13      |
| <b>Barrel Size</b>   | 30mm                     |
| <b>Action</b>        | Momentary                |
| <b>Bulb Type</b>     | Incandescent illuminated |
| <b>Contact Type</b>  | Operator only            |
| <b>Base Material</b> | Metal                    |

|                           |              |
|---------------------------|--------------|
| <b>Bezel Material</b>     | Metal        |
| <b>Operator Color</b>     | Yellow       |
| <b>Operator Type</b>      | Extended     |
| <b>Operator Size</b>      | 28mm         |
| <b>Operator Shape</b>     | Round        |
| <b>Operator Material</b>  | Plastic      |
| <b>Voltage Rating</b>     | 24 VAC/VDC   |
| <b>Voltage Regulation</b> | Full voltage |

## Agency Approvals

|                             |  |
|-----------------------------|--|
| <b>UL Listed File #</b>     | E131568                                |
| <b>UL Recognized File #</b> | None                                   |
| <b>UL Hazardous File #</b>  | None                                   |
| <b>CE</b>                   | <a href="#">View CE declarations</a>   |
| <b>CSA File #</b>           | 68551                                  |
| <b>RoHS Status</b>          | Yes (See CE Doc)                       |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a> |