

HT8GDABV3 Cut Sheet



Eaton pushbutton, 30mm, momentary, incandescent illuminated, (1) N.C. contact(s), metal base, metal bezel, guarded, Operator: amber, flush, 28mm, round, plastic, 24 VAC/VDC, full voltage.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/HT8GDABV3>

Technical Specifications

| | |
|----------------------------|--------------------------|
| Brand | Eaton |
| Item | Pushbutton |
| NEMA Rating | 1/2/3/3R/4/4X/12/13 |
| Barrel Size | 30mm |
| Action | Momentary |
| Bulb Type | Incandescent illuminated |
| Contact Type | (1) N.C. |
| Base Material | Metal |
| Bezel Material | Metal |
| Operator Protection | Guarded |
| Operator Color | Amber |
| Operator Type | Flush |
| Operator Size | 28mm |
| Operator Shape | Round |
| Operator Material | Plastic |
| Voltage Rating | 24 VAC/VDC |
| Voltage Regulation | Full voltage |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | E131568 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | 68551 |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |