

HT8GDYF7 Cut Sheet



Eaton pushbutton, 30 mm, momentary, LED illuminated, operator only, metal base, metal bezel, guarded, Operator: yellow, flush, 28 mm, round, plastic, 120 VAC/VDC, full voltage.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/HT8GDYF7>

Technical Specifications

Brand	Eaton
Item	Pushbutton
NEMA Rating	1/2/3/3R/4/4X/12/13
Barrel Size	30 mm
Action	Momentary
Bulb Type	LED illuminated
Contact Type	Operator only
Base Material	Metal
Bezel Material	Metal

Operator Protection	Guarded
Operator Color	Yellow
Operator Type	Flush
Operator Size	28 mm
Operator Shape	Round
Operator Material	Plastic
Voltage Rating	120 VAC/VDC
Voltage Regulation	Full voltage

Agency Approvals

UL Listed File #	E131568
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	68551
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document