

# HT8GVBV7 Cut Sheet



Eaton incandescent indicating light, permanent light function, 30mm, push-to-test, blue, 32mm, round, metal base, metal bezel, 120 VAC/VDC, full voltage.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/HT8GVBV7>

## Technical Specifications

<b>Brand</b>	Eaton
<b>Item</b>	Indicating light
<b>Bulb Type</b>	Incandescent
<b>Light Function</b>	Permanent
<b>NEMA Rating</b>	1/2/3/3R/4/4X/12/13
<b>Barrel Size</b>	30mm
<b>Action</b>	Push-to-test
<b>Contact Type</b>	Operator only

<b>Operator Color</b>	Blue
<b>Light Color(s)</b>	Blue
<b>Operator Size</b>	32mm
<b>Operator Shape</b>	Round
<b>Base Material</b>	Metal
<b>Bezel Material</b>	Metal
<b>Voltage Rating</b>	120 VAC/VDC
<b>Voltage Regulation</b>	Full voltage

## Agency Approvals

<b>UL Listed File #</b>	E131568
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	68551
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>