

HT8GVGV7 Cut Sheet



Eaton incandescent indicating light, permanent light function, 30mm, push-to-test, green, 32mm, round, metal base, metal bezel, 120 VAC/VDC, full voltage.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/HT8GVGV7>

Technical Specifications

| | |
|--------------------|---------------------|
| Brand | Eaton |
| Item | Indicating light |
| Bulb Type | Incandescent |
| Light Function | Permanent |
| NEMA Rating | 1/2/3/3R/4/4X/12/13 |
| Barrel Size | 30mm |
| Action | Push-to-test |
| Contact Type | Operator only |
| Operator Color | Green |
| Light Color(s) | Green |
| Operator Size | 32mm |
| Operator Shape | Round |
| Base Material | Metal |
| Bezel Material | Metal |
| Voltage Rating | 120 VAC/VDC |
| Voltage Regulation | Full voltage |

Agency Approvals

| | |
|----------------------|--|
| UL Listed File # | E131568 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | 68551 |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |