

HT8GVRV7 Cut Sheet



Eaton incandescent indicating light, permanent light function, 30mm, push-to-test, red, 32mm, round, metal base, metal bezel, 120 VAC/VDC, full voltage.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/HT8GVRV7>

Technical Specifications

Brand	Eaton
Item	Indicating light
Bulb Type	Incandescent
Light Function	Permanent
NEMA Rating	1/2/3/3R/4/4X/12/13
Barrel Size	30mm
Action	Push-to-test
Contact Type	Operator only
Operator Color	Red
Light Color(s)	Red
Operator Size	32mm
Operator Shape	Round
Base Material	Metal
Bezel Material	Metal
Voltage Rating	120 VAC/VDC
Voltage Regulation	Full voltage

Agency Approvals

UL Listed File #	E131568
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	68551
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document