

HT8GVWV3 Cut Sheet



Eaton incandescent indicating light, permanent light function, 30mm, push-to-test, white, 32mm, round, metal base, metal bezel, 24 VAC/VDC, full voltage.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/HT8GVWV3>

Technical Specifications

Brand	Eaton	Operator Color	White
Item	Indicating light	Light Color(s)	White
Bulb Type	Incandescent	Operator Size	32mm
Light Function	Permanent	Operator Shape	Round
NEMA Rating	1/2/3/3R/4/4X/12/13	Base Material	Metal
Barrel Size	30mm	Bezel Material	Metal
Action	Push-to-test	Voltage Rating	24 VAC/VDC
Contact Type	Operator only	Voltage Regulation	Full voltage

Agency Approvals

UL Listed File #	E131568
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	68551
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document