

# HT8HFWV3 Cut Sheet



Eaton incandescent indicating light, permanent light function, 30mm, white, 32mm, round, metal base, metal bezel, 24 VAC/VDC, full voltage.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/HT8HFWV3>

## Technical Specifications

|                           |                     |
|---------------------------|---------------------|
| <b>Brand</b>              | Eaton               |
| <b>Item</b>               | Indicating light    |
| <b>Bulb Type</b>          | Incandescent        |
| <b>Light Function</b>     | Permanent           |
| <b>NEMA Rating</b>        | 1/2/3/3R/4/4X/12/13 |
| <b>Barrel Size</b>        | 30mm                |
| <b>Contact Type</b>       | Operator only       |
| <b>Operator Color</b>     | White               |
| <b>Light Color(s)</b>     | White               |
| <b>Operator Size</b>      | 32mm                |
| <b>Operator Shape</b>     | Round               |
| <b>Base Material</b>      | Metal               |
| <b>Bezel Material</b>     | Metal               |
| <b>Voltage Rating</b>     | 24 VAC/VDC          |
| <b>Voltage Regulation</b> | Full voltage        |

## Agency Approvals

|                             |  |
|-----------------------------|--|
| <b>UL Listed File #</b>     | E131568                                |
| <b>UL Recognized File #</b> | None                                   |
| <b>UL Hazardous File #</b>  | None                                   |
| <b>CE</b>                   | <a href="#">View CE declarations</a>   |
| <b>CSA File #</b>           | 68551                                  |
| <b>RoHS Status</b>          | Yes (See CE Doc)                       |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a> |