

# HVS-53C12 Cut Sheet



NITRA solenoid valve, ISO 5599/1 size 1, 5-way, 3-position, center closed, double solenoid, aluminum alloy body, locking manual override.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/HVS-53C12>

## Technical Specifications

<b>Brand</b>	NITRA
<b>Series</b>	ISO 5599/1 Valves (HSV)
<b>Item</b>	Valve
<b>Working Fluid</b>	Air
<b>Valve Type</b>	Solenoid directional control
<b>Port Quantity</b>	5-way
<b>Number Of Positions</b>	3
<b>Valve Configuration</b>	Center closed
<b>Action</b>	Double solenoid
<b>Body Material</b>	Aluminum alloy

<b>Manual Override Type</b>	Locking
<b>Maximum Operating Pressure</b>	145 psi (10 bar)
<b>Minimum Operating Pressure</b>	37 psi (2.5 bar)
<b>Form Factor</b>	ISO 5599/1 size 1
<b>Includes</b>	Captive mounting screws and solenoid coil nut
<b>Requires</b>	Stand-alone base or manifold
<b>Additional Information</b>	Purchase solenoid coil in desired voltage separately

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/HVS-53C12.pdf>  
See store item page for other formats.