HVS-53P22 Cut Sheet

AUTOMATIONDIRECT.com
www.automationdirect.com

NITRA pneumatic solenoid valve, ISO 5599/1 size 2, 5-way, 3-position, center pressure, double solenoid, aluminum alloy body, locking manual override.

For complete product information, please see this item on our store at the following link:

https://www.automationdirect.com/pn/HVS-53P22

Technical Specifications

Brand	NITRA
Item	Valve
Working Fluid	Air
Valve Type	Solenoid directional control
Port Quantity	5-way
Number Of Positions	3
Valve Configuration	Center pressure
Action	Double solenoid
Body Material	Aluminum alloy
Seal Material	Nitrile

Manual Override Type	Locking
Maximum Operating Pressure	145 psi (10 bar)
Minimum Operating Pressure	37 psi (2.5 bar)
Working Fluid Temperature	14–140 °F
Form Factor	ISO 5599/1 size 2
Includes	Captive mounting screws and solenoid coil nut
Requires	Stand-alone base or manifold
Additional Information	Purchase solenoid coil in desired voltage separately

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings

2D Drawing PDF Link:
https://cdn.automationdirect.com/static/drawings/2d/HVS-53P22.pdf
See store item page for other formats.