

HVU14-P Cut Sheet



HydroMode potable water push-to-connect fitting, union straight manual hand valve, acetal body, (2) 1/4in tube connection(s), NSF/ANSI 61. Package of 2.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/HVU14-P>

Technical Specifications

Brand	HydroMode
Item	Fitting
Working Fluid	Potable water
Fitting Connection Type	Push-to-connect
Fitting Type	Union straight manual hand valve
Body Material	Acetal
Connection	(2) 1/4in push-to-connect
Operating Pressure	145 psi
Operating Temperature	32 to 158 deg F
Potable Water Certifications	NSF/ANSI 61
Quantity per Pack	2

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/HVU14-P.pdf>
See store item page for other formats.