

HVU516-3L Cut Sheet



NITRA pneumatic push-to-connect fitting, inline manual shutoff valve, locking, 3-way, technopolymer body, (1) 5/16in (8mm) push-to-connect to (1) 5/16in (8mm) push-to-connect.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/HVU516-3L>

Technical Specifications

Brand	NITRA
Item	Fitting
Working Fluid	Air or inert gas
Fitting Connection Type	Push-to-connect
Fitting Type	Inline manual shutoff valve
Fitting Function	Locking
Valve Function	3-way
Body Material	Technopolymer

Fitting Measurement Type	Metric and SAE
Connection	(1) 5/16in (8mm) push-to-connect to (1) 5/16in (8mm) push-to-connect
Operating Pressure	150 psi
Operating Temperature	-4 to 140 deg F
For Use With	Flexible pneumatic tubing
Includes	Lock and 2 keys

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/HVU516-3L.pdf>
See store item page for other formats.