

# HW-J100805CHTL Cut Sheet



Wiegmann JIC series enclosure, NEMA 1/3R/4X/6P/12, 10 x 8 x 5in (HxWxD), wall mount, fiberglass reinforced polyester, gray, crowned single-door, (1) twist-lock latch.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/HW-J100805CHTL>

## Technical Specifications

<b>Brand</b>	Wiegmann
<b>Item</b>	Enclosure
<b>Series</b>	JIC
<b>Subpanel</b>	Purchase subpanel separately
<b>Slope Top</b>	No
<b>NEMA Rating</b>	1/3R/4X/6P/12
<b>Nominal Enclosure Height</b>	10in
<b>Nominal Enclosure Width</b>	8in
<b>Nominal Enclosure Depth</b>	5in
<b>Mounting</b>	Wall
<b>Integral Mounting Feet</b>	No

<b>Integral Mounting Flange</b>	Yes
<b>Dual Access</b>	No
<b>Knockouts</b>	No
<b>Material</b>	Fiberglass reinforced polyester
<b>Color</b>	Gray
<b>Cover Type</b>	Crowned single-door
<b>Hinge Type</b>	Continuous hinge
<b>Number of Hinges Per Door</b>	1
<b>Latch Type</b>	(1) twist-lock latch
<b>Padlockable</b>	No
<b>Keylocking</b>	No

## Agency Approvals

<b>UL Listed File #</b>	E64791
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/HW-J100805CHTL.pdf>  
See store item page for other formats.