

HW-J80804CHTL Cut Sheet



Wiegmann JIC series enclosure, NEMA 1/3R/4X/6P/12, 8 x 8 x 4in (HxWxD), wall mount, fiberglass reinforced polyester, gray, single-door, (1) twist-lock latch.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/HW-J80804CHTL>

Technical Specifications

Brand	Wiegmann	Integral Mounting Flange	Yes
Item	Enclosure	Dual Access	No
Series	JIC	Knockouts	No
Subpanel	Purchase subpanel separately	Material	Fiberglass reinforced polyester
Slope Top	No	Color	Gray
NEMA Rating	1/3R/4X/6P/12	Cover Type	Single-door
Nominal Enclosure Height	8in	Hinge Type	Continuous hinge
Nominal Enclosure Width	8in	Number of Hinges Per Door	1
Nominal Enclosure Depth	4in	Latch Type	(1) twist-lock latch
Mounting	Wall	Padlockable	No
Integral Mounting Feet	No	Keylocking	No

Agency Approvals

UL Listed File #	E64791
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/HW-J80804CHTL.pdf>
See store item page for other formats.