

HW-N4X532 Cut Sheet



Wiegmann Slim Line series enclosure, NEMA 1/3R/4X/6P/12, 5 x 3 x 2in (HxWxD), wall mount, fiberglass reinforced polyester, gray, crowned screw cover.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/HW-N4X532>

Technical Specifications

Brand	Wiegmann
Item	Enclosure
Series	Slim Line
Subpanel	Purchase subpanel separately
Slope Top	No
NEMA Rating	1/3R/4X/6P/12
Nominal Enclosure Height	5in
Nominal Enclosure Width	3in
Nominal Enclosure Depth	2in
Mounting	Wall

Integral Mounting Feet	No
Integral Mounting Flange	No
Dual Access	No
Knockouts	No
Material	Fiberglass reinforced polyester
Color	Gray
Cover Type	Crowned screw cover
Padlockable	No
Keylocking	No

Agency Approvals

UL Listed File #	E64791
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/HW-N4X532.pdf>
See store item page for other formats.