

HW24168SSHK Cut Sheet



Hammond enclosure, NEMA 3R/4/4X/12/13, 24 x 16 x 8in (HxWxD), wall mount, 304 stainless steel, #4 brush finish, single-door, 3-point 316 stainless steel padlocking handle.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/HW24168SSHK>

Technical Specifications

Brand	Hammond	Integral Mounting Flange	No
Item	Enclosure	Dual Access	No
Subpanel	Purchase subpanel separately	Knockouts	No
Slope Top	No	Bottom Gland Plate	No
3-Piece Assembly	No	Material	304 stainless steel
Vented	No	Finish	#4 brush
NEMA Rating	3R/4/4X/12/13	Cover Type	Single-door
IP Rating	IP66	Hinge Type	Continuous hinge
Nominal Enclosure Dimensions	24 x 16 x 8in (HxWxD)	Number of Hinges Per Door	1
Enclosure Height	24.00in	Latch Type	3-point 316 stainless steel padlocking handle
Enclosure Width	16.00in	Number Of Latches	1
Enclosure Depth	9.21in	Shelf	No
Mounting	Wall	Padlockable	Yes
Integral Mounting Feet	Yes	Keylocking	No

Agency Approvals

UL Listed File #	E65324
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	LR21001
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/HW24168SSHK.pdf>
See store item page for other formats.