

HWST201612S16 Cut Sheet



Hammond Waterfall series enclosure, slope top, NEMA 3R/4/4X/12/13, 20 x 16 x 12in (HxWxD), wall mount, 316 stainless steel, #4 brush finish, single-door, 1/4-turn semi-flush stainless steel.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/HWST201612S16>

Technical Specifications

Brand	Hammond
Item	Enclosure
Series	Waterfall
Subpanel	Purchase subpanel separately
Slope Top	Yes
3-Piece Assembly	No
Vented	No
NEMA Rating	3R/4/4X/12/13
IP Rating	IP69K
Nominal Enclosure Dimensions	20 x 16 x 12in (HxWxD)
Enclosure Height	25.59in
Enclosure Width	16.00in
Enclosure Depth	13.21in
Mounting	Wall
Integral Mounting Feet	No

Integral Mounting Flange	No
Dual Access	No
Knockouts	No
Bottom Gland Plate	No
Material	316 stainless steel
Finish	#4 brush
Cover Type	Single-door
Hinge Type	External bullet
Number of Hinges Per Door	2
Latch Type	1/4-turn semi-flush stainless steel
Number Of Latches	2
Shelf	No
Padlockable	No
Keylocking	No

Agency Approvals

UL Listed File #	E65324
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	LR21001
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/HWST201612S16.pdf>
See store item page for other formats.