

HYJ14116SS Cut Sheet



Hammond sanitary enclosure, slope top, NEMA 3R/4/4X/12, 14 x 11 x 6in (HxWxD), wall mount, 304 stainless steel, #4 brush finish, screw cover.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/HYJ14116SS>

Technical Specifications

Brand	Hammond
Item	Sanitary enclosure
Subpanel	Purchase subpanel separately
Slope Top	Yes
3-Piece Assembly	No
Vented	No
NEMA Rating	3R/4/4X/12
IP Rating	IP69K
Nominal Enclosure Dimensions	14 x 11 x 6in (HxWxD)
Enclosure Height	14.15in
Enclosure Width	11.19in
Enclosure Depth	6.53in
Mounting	Wall

Integral Mounting Feet	No
Integral Mounting Flange	No
Dual Access	No
Knockouts	No
Bottom Gland Plate	No
Material	304 stainless steel
Finish	#4 brush
Cover Type	Screw cover
Shelf	No
Padlockable	No
Keylocking	No
Includes	Mounting hardware

Agency Approvals

UL Listed File #	E517628/E65324
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/HYJ14116SS.pdf>
See store item page for other formats.