

IHSKITIMP Cut Sheet



MK Morse hole saw set, 3 pieces, bi-metal cobalt, hardened steel backer, straight pitch.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/IHSKITIMP>

Technical Specifications

Brand	MK Morse	Tooth Density	8 teeth/in
Item	Hole saw set	Toothing	Straight pitch
Number of Pieces	3	Set Includes	Includes (3) bi-metal impact hole saws with 1/4in shank and integrated pilot drill (7/8in (22mm), 1-1/8in (29mm), 1-3/8in (35mm))
Material	Bi-metal cobalt	Application	Hole cutting
Hole Saw Size	7/8in (22mm), 1-1/8in (29mm) and 1-3/8in (35mm)	For Use On	Sheet metal
Cutting Direction	Right hand	Additional Information	Integrated spring for quick slug removal
Hardened Steel Backer	Yes		

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement