

IISRB-500-1 Cut Sheet



Penn-Union pre-insulated splicer/reducer, in-line entry, 1 port, aluminum, 3/8in hex conductor bolt, 6 AWG-500 MCM, AL9CU.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/IISRB-500-1>

Technical Specifications

Brand	Penn-Union
Item	Splicer/reducer
Power Bar Type	Pre-insulated
Entry Type	In-line
Number Of Conductor Ports	1
Material	Aluminum
Color	Black

Conductor Bolt Style	3/8in hex
Conductor Size	6 AWG-500 MCM
Conductor Material	Copper or aluminum
Voltage Rating	600V
Dual Rating	AL9CU
Includes	Oxide inhibitor

Agency Approvals

UL Listed File #	E12822
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/IISRB-500-1.pdf>
See store item page for other formats.