

# IM4-6-BD-8-1-4-N-B Cut Sheet



CITO Inline air, coolant, oil or water manifold, anodized aluminum, blue, rectangular, 3000 psi maximum operating pressure, (4) stations, (2) 1in female NPT inlet(s), (8) 1/4in female NPT outlet(s), 45-deg and 135-deg orientation.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/IM4-6-BD-8-1-4-N-B>

## Technical Specifications

<b>Brand</b>	CITO
<b>Item</b>	Manifold
<b>Series</b>	Inline
<b>Working Fluid</b>	Pneumatic, coolant, oil or water
<b>Material</b>	Anodized aluminum
<b>Color</b>	Blue
<b>Shape</b>	Rectangular
<b>Body Length</b>	6.25in
<b>Number of Stations</b>	4
<b>Maximum Operating Pressure</b>	3000 psi
<b>Inlet Port</b>	(2) 1in female NPT
<b>Outlet Port</b>	(8) 1/4in female NPT
<b>Hole Orientation</b>	45-deg and 135-deg
<b>Includes</b>	IM-3040 end cap and mounting screws

## Agency Approvals

<b>CE</b>	None
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/IM4-6-BD-8-1-4-N-B.pdf>  
See store item page for other formats.