


IM4-6-BD-8-3-8-N-R Cut Sheet



CITO Inline air, coolant, oil or water manifold, anodized aluminum, red, rectangular, 3000 psi maximum operating pressure, (4) stations, (2) 1in female NPT inlet(s), (8) 3/8in female NPT outlet(s), 45-deg and 135-deg orientation.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/IM4-6-BD-8-3-8-N-R>

Technical Specifications

Brand	CITO
Item	Manifold
Series	Inline
Working Fluid	Pneumatic, coolant, oil or water
Material	Anodized aluminum
Color	Red
Shape	Rectangular
Body Length	6.25in
Number of Stations	4
Maximum Operating Pressure	3000 psi
Inlet Port	(2) 1in female NPT
Outlet Port	(8) 3/8in female NPT
Hole Orientation	45-deg and 135-deg
Includes	IM-3040 end cap and mounting screws

Agency Approvals

CE	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/IM4-6-BD-8-3-8-N-R.pdf>
See store item page for other formats.