

IM6-14-BD-12-1-2-N-B Cut Sheet



CITO Inline air, coolant, oil or water manifold, anodized aluminum, blue, rectangular, 3000 psi maximum operating pressure, (6) stations, (2) 1-1/2in female NPT inlet(s), (12) 1/2in female NPT outlet(s), 45-deg and 135-deg orientation.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/IM6-14-BD-12-1-2-N-B>

Technical Specifications

Brand	CITO
Item	Manifold
Series	Inline
Working Fluid	Pneumatic, coolant, oil or water
Material	Anodized aluminum
Color	Blue
Shape	Rectangular
Body Length	14in
Number of Stations	6
Maximum Operating Pressure	3000 psi
Inlet Port	(2) 1-1/2in female NPT
Outlet Port	(12) 1/2in female NPT
Hole Orientation	45-deg and 135-deg
Includes	IM-3060 end cap and mounting screws

Agency Approvals

CE	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/IM6-14-BD-12-1-2-N-B.pdf>
See store item page for other formats.