

# INCH-3-223002 Cut Sheet



IDEM safety switch, tongue (key) interlock, slow action break before make, (2) N.C. safety output(s), plastic body, 316 stainless steel head, (1) 8-pin M12 quick-disconnect.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/INCH-3-223002>

## Technical Specifications

|                               |                                |
|-------------------------------|--------------------------------|
| <b>Brand</b>                  | IDEM                           |
| <b>Item</b>                   | Safety switch                  |
| <b>Actuator Type</b>          | Tongue (key) interlock         |
| <b>Head Type</b>              | 90-degree adjustable           |
| <b>Action</b>                 | Slow action break before make  |
| <b>Safety Output Type</b>     | (2) N.C.                       |
| <b>Monitoring Output Type</b> | (1) N.O.                       |
| <b>Housing Size</b>           | 25 x 103 x 29mm                |
| <b>Body Material</b>          | Plastic                        |
| <b>Head Material</b>          | 316 stainless steel            |
| <b>IP Rating</b>              | IP67                           |
| <b>Connection</b>             | (1) 8-pin M12 quick-disconnect |
| <b>Cable Length</b>           | 9.8in/250mm                    |

## Agency Approvals

|                             |                                        |
|-----------------------------|----------------------------------------|
| <b>UL Listed File #</b>     | E258676                                |
| <b>UL Recognized File #</b> | None                                   |
| <b>UL Hazardous File #</b>  | None                                   |
| <b>CE</b>                   | <a href="#">View CE declarations</a>   |
| <b>CSA File #</b>           | None                                   |
| <b>RoHS Status</b>          | Yes (See CE Doc)                       |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a> |