

IP500U75 Cut Sheet



International Power unregulated linear power supply, 75 VDC @ 6.6A/480W, 120/240 VAC nominal input, 1-phase, open frame, aluminum housing, chassis mount, screw and spade.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/IP500U75>

Technical Specifications

Brand	International Power	Remote On/Off	No
Item	Power supply	Voltage Monitoring	No
Power Supply Type	Unregulated linear	Enclosure Type	Open frame
Efficiency	75% @ 120 VAC	Housing Material	Aluminum
Output Configuration	Single output	Mounting	Chassis
Output	75 VDC @ 6.6A/480W	Connector Type	Screw and spade
Input voltage range	120/240 VAC	NEC Class 2	No
Input Voltage Selection Type	Jumper	Integrated UPS Battery Control	No
Number of Input Phases	1	Operating Temperature	0 to 55 deg C
Protection Type(s)	short circuit		

Agency Approvals

UL Listed File #	None
UL Recognized File #	E133338
UL Hazardous File #	None
CE	View CE declarations
CSA File #	C22.2 No. 1950
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/IP500U75.pdf>
See store item page for other formats.