

# IPBB-NA250-3D-1 Cut Sheet



Penn-Union pre-insulated power bar, double-sided entry, 3 ports, aluminum, 5/16in hex conductor bolt, 10 AWG-250 MCM, AL9CU.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/IPBB-NA250-3D-1>

## Technical Specifications

|                                  |               |
|----------------------------------|---------------|
| <b>Brand</b>                     | Penn-Union    |
| <b>Item</b>                      | Power bar     |
| <b>Power Bar Type</b>            | Pre-insulated |
| <b>Entry Type</b>                | Double-sided  |
| <b>Number Of Conductor Ports</b> | 3             |
| <b>Material</b>                  | Aluminum      |
| <b>Color</b>                     | Black         |

|                             |                    |
|-----------------------------|--------------------|
| <b>Conductor Bolt Style</b> | 5/16in hex         |
| <b>Conductor Size</b>       | 10 AWG-250 MCM     |
| <b>Conductor Material</b>   | Copper or aluminum |
| <b>Voltage Rating</b>       | 600V               |
| <b>Dual Rating</b>          | AL9CU              |
| <b>Includes</b>             | Oxide inhibitor    |

## Agency Approvals

|                             |   |
|-----------------------------|---|
| <b>UL Listed File #</b>     | E12822  |
| <b>UL Recognized File #</b> | None  |
| <b>UL Hazardous File #</b>  | None  |
| <b>CSA File #</b>           | None  |
| <b>RoHS Status</b>          | Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below) |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a>                              |
| <b>Other</b>                | <a href="#">RoHS Statement</a>                                      |

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/IPBB-NA250-3D-1.pdf>  
See store item page for other formats.