

IPBB-NA2/0-2S-1 Cut Sheet



Penn-Union pre-insulated power bar, single-sided entry, 2 ports, aluminum, 7/32in hex conductor bolt, 14-2/0 AWG, AL9CU.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/IPBB-NA2/0-2S-1>

Technical Specifications

Brand	Penn-Union
Item	Power bar
Power Bar Type	Pre-insulated
Entry Type	Single-sided
Number Of Conductor Ports	2
Material	Aluminum
Color	Black

Conductor Bolt Style	7/32in hex
Conductor Size	14-2/0 AWG
Conductor Material	Copper or aluminum
Voltage Rating	600V
Dual Rating	AL9CU
Includes	Oxide inhibitor

Agency Approvals

UL Listed File #	E12822
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
https://cdn.automationdirect.com/static/drawings/2d/IPBB-NA2_0-2S-1.pdf
See store item page for other formats.