

# ISEUR1 Cut Sheet



Macromatic intrinsically safe relay, 35mm DIN rail mount, finger-safe, Discrete Input: 1-point, 10 VDC input voltage, 102-132 VAC or 10-125 VDC coil voltage, Discrete Output: 1-point, relay, SPST, 5A contact rating, (1) N.O., LED indicator(s).

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/ISEUR1>

## Technical Specifications

<b>Brand</b>	Macromatic
<b>Relay Type</b>	Intrinsically safe
<b>Item</b>	Relay
<b>Mounting</b>	35mm DIN rail
<b>Relay Housing Type</b>	Finger-safe
<b>Number of Discrete Input Points</b>	1
<b>Input Voltage</b>	10 VDC
<b>Coil Voltage</b>	102-132 VAC or 10-125 VDC
<b>Number of Discrete Output Points</b>	1
<b>Discrete Output Type</b>	Relay
<b>Relay Configuration</b>	SPST
<b>Contact Rating</b>	5A
<b>Output Type</b>	(1) N.O.
<b>Connector Type</b>	Screw terminal(s)
<b>Indicator</b>	LED
<b>Application</b>	Hazardous location rated

## Agency Approvals

<b>UL Listed File #</b>	E318075
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	E318075
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>