

J1008W Cut Sheet



Stahlin J series enclosure, NEMA 1/3R/4X/6P/12, 10 x 8 x 4in (HxWxD), wall mount, fiberglass reinforced polyester, gray, screw cover, integral mounting flange.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/J1008W>

Technical Specifications

Brand	Stahlin
Series	J
Item	Enclosure
Subpanel	Purchase subpanel separately
NEMA Rating	1/3R/4X/6P/12
IP Rating	IP66
Nominal Enclosure Height	10in
Nominal Enclosure Width	8in
Nominal Enclosure Depth	4in
Mounting	Wall

Integral Mounting Feet	No
Integral Mounting Flange	Yes
Knockouts	No
Material	Fiberglass reinforced polyester
Color	Gray
Cover Type	Screw cover
Padlockable	No
Keylocking	No
Shelf	No

Agency Approvals

UL Listed File #	E64358	E362920
UL Recognized File #	E333478	
UL Hazardous File #	None	
CE	View CE declarations	
CSA File #	LR069014	
RoHS Status	Yes (See CE Doc)	
EU REACH	View EU REACH document	

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/J1008W.pdf>
See store item page for other formats.