

# J181617SSH Cut Sheet



Stahlin FatBoy series enclosure, NEMA 1/3/4X/12, 18 x 16 x 17in (HxWxD), wall mount, fiberglass reinforced polyester, gray, clamshell single-door, (2) twist-lock latches, padlock hasp and staple.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/J181617SSH>

## Technical Specifications

<b>Brand</b>	Stahlin
<b>Item</b>	Enclosure
<b>Series</b>	FatBoy
<b>Subpanel</b>	Purchase subpanel separately
<b>Slope Top</b>	No
<b>3-Piece Assembly</b>	No
<b>Vented</b>	No
<b>NEMA Rating</b>	1/3/4X/12
<b>IP Rating</b>	IP66
<b>Nominal Enclosure Dimensions</b>	18 x 16 x 17in (HxWxD)
<b>Enclosure Height</b>	19.63in
<b>Enclosure Width</b>	16.92in
<b>Enclosure Depth</b>	17.19in
<b>Mounting</b>	Wall
<b>Integral Mounting Feet</b>	No

<b>Integral Mounting Flange</b>	Yes
<b>Dual Access</b>	No
<b>Knockouts</b>	No
<b>Bottom Gland Plate</b>	No
<b>Material</b>	Fiberglass reinforced polyester
<b>Color</b>	Gray
<b>Cover Type</b>	Clamshell single-door
<b>Hinge Type</b>	Continuous hinge
<b>Number of Hinges Per Door</b>	1
<b>Latch Type</b>	(2) twist-lock latches
<b>Padlock Attachment Type</b>	Padlock hasp and staple
<b>Shelf</b>	No
<b>Padlockable</b>	Yes
<b>Keylocking</b>	No

## Agency Approvals

<b>UL Listed File #</b>	E64358
<b>UL Recognized File #</b>	E333478
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	LR069014
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/J181617SSH.pdf>  
See store item page for other formats.