

# J1816W Cut Sheet



Stahlin J series enclosure, NEMA 1/3R/4X/6P/12, 18 x 16 x 8in (HxWxD), wall mount, fiberglass reinforced polyester, gray, screw cover.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/J1816W>

## Technical Specifications

<b>Brand</b>	Stahlin
<b>Item</b>	Enclosure
<b>Series</b>	J
<b>Subpanel</b>	Purchase subpanel separately
<b>Slope Top</b>	No
<b>NEMA Rating</b>	1/3R/4X/6P/12
<b>IP Rating</b>	IP66
<b>Nominal Enclosure Dimensions</b>	18 x 16 x 8in (HxWxD)
<b>Enclosure Height</b>	19.62in
<b>Enclosure Width</b>	17.61in
<b>Enclosure Depth</b>	8.82in
<b>Mounting</b>	Wall
<b>Integral Mounting Feet</b>	No
<b>Integral Mounting Flange</b>	Yes
<b>Dual Access</b>	No
<b>Knockouts</b>	No
<b>Material</b>	Fiberglass reinforced polyester
<b>Color</b>	Gray
<b>Cover Type</b>	Screw cover
<b>Padlockable</b>	No
<b>Keylocking</b>	No

## Agency Approvals

<b>UL Listed File #</b>	E64358	E362920
<b>UL Recognized File #</b>	E333478	
<b>UL Hazardous File #</b>	None	
<b>CE</b>	<a href="#">View CE declarations</a>	
<b>CSA File #</b>	LR069014	
<b>RoHS Status</b>	Yes (See CE Doc)	
<b>EU REACH</b>	<a href="#">View EU REACH document</a>	