

J2016HLL Cut Sheet



Stahlin J series enclosure, NEMA 1/3R/4X/6P/12, 20 x 16 x 8in (HxWxD), wall mount, fiberglass reinforced polyester, gray, single-door, (2) twist-lock latches.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/J2016HLL>

Technical Specifications

Brand	Stahlin	Integral Mounting Feet	No
Item	Enclosure	Integral Mounting Flange	Yes
Series	J	Dual Access	No
Subpanel	Purchase subpanel separately	Knockouts	No
Slope Top	No	Bottom Gland Plate	No
3-Piece Assembly	No	Material	Fiberglass reinforced polyester
Vented	No	Color	Gray
NEMA Rating	1/3R/4X/6P/12	Cover Type	Single-door
IP Rating	IP66	Hinge Type	Continuous hinge
Nominal Enclosure Dimensions	20 x 16 x 8in (HxWxD)	Number of Hinges Per Door	1
Enclosure Height	22.00in	Latch Type	(2) twist-lock latches
Enclosure Width	17.68in	Shelf	No
Enclosure Depth	8.81in	Padlockable	No
Mounting	Wall	Keylocking	No

Agency Approvals

UL Listed File #	E64358	E362920
UL Recognized File #	E333478	
UL Hazardous File #	None	
CE	View CE declarations	
CSA File #	LR069014	
RoHS Status	Yes (See CE Doc)	
EU REACH	View EU REACH document	

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/J2016HLL.pdf>
See store item page for other formats.