


J20MD-M Cut Sheet



NITRA pneumatic rotary actuator, double acting, size 20, 0 to 190 degrees, rubber bumpers, anodized aluminum body, M5 x 0.8 threaded port(s).

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/J20MD-M>

Technical Specifications

Brand	NITRA
Item	Rotary actuator
Working Fluid	Pneumatic
Action Type	Double acting
Size	20
Adjustable Travel	0 to 190 degrees
Cushion Type	Rubber bumpers
Body Material	Anodized aluminum
Port Information	M5 x 0.8 threaded

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document