

J3024HPL Cut Sheet



Stahlin J series enclosure, NEMA 1/3/3R/4/4X/12/13, 30 x 24 x 10in (HxWxD), wall mount, fiberglass reinforced polyester, Pantone 428 C glacier gray, single-door, (5) quick-release latches, padlock hasp and staple.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/J3024HPL>

Technical Specifications

Brand	Stahlin
Item	Enclosure
Series	J
Subpanel	Purchase subpanel separately
Slope Top	No
3-Piece Assembly	No
Vented	No
NEMA Rating	1/3/3R/4/4X/12/13
IP Rating	IP66
Nominal Enclosure Dimensions	30 x 24 x 10in (HxWxD)
Enclosure Height	32.19in
Enclosure Width	26.18in
Enclosure Depth	12.26in
Mounting	Wall
Integral Mounting Feet	Yes

Integral Mounting Flange	No
Dual Access	No
Knockouts	No
Bottom Gland Plate	No
Material	Fiberglass reinforced polyester
Color	Pantone 428 C glacier gray
Cover Type	Single-door
Hinge Type	Continuous hinge
Number of Hinges Per Door	1
Latch Type	(5) quick-release latches
Padlock Attachment Type	Padlock hasp and staple
Shelf	No
Padlockable	Yes
Keylocking	No

Agency Approvals

UL Listed File #	E64358
UL Recognized File #	E333478
UL Hazardous File #	None
CE	View CE declarations
CSA File #	LR069014
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/J3024HPL.pdf>
See store item page for other formats.