

J604HLL Cut Sheet



Stahlin J series enclosure, NEMA 1/3R/4X/6P/12, 6 x 4 x 4in (HxWxD), wall mount, fiberglass reinforced polyester, gray, single-door, (1) twist-lock latch.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/J604HLL>

Technical Specifications

| | |
|-------------------------------------|------------------------------|
| Brand | Stahlin |
| Item | Enclosure |
| Series | J |
| Subpanel | Purchase subpanel separately |
| Slope Top | No |
| NEMA Rating | 1/3R/4X/6P/12 |
| IP Rating | IP66 |
| Nominal Enclosure Dimensions | 6 x 4 x 4in (HxWxD) |
| Enclosure Height | 7.47in |
| Enclosure Width | 5.45in |
| Enclosure Depth | 4.70in |
| Mounting | Wall |

| | |
|----------------------------------|---------------------------------|
| Integral Mounting Feet | No |
| Integral Mounting Flange | Yes |
| Dual Access | No |
| Knockouts | No |
| Material | Fiberglass reinforced polyester |
| Color | Gray |
| Cover Type | Single-door |
| Hinge Type | Continuous hinge |
| Number of Hinges Per Door | 1 |
| Latch Type | (1) twist-lock latch |
| Padlockable | No |
| Keylocking | No |

Agency Approvals

| | | |
|-----------------------------|--|---------|
| UL Listed File # | E64358 | E362920 |
| UL Recognized File # | E333478 | |
| UL Hazardous File # | None | |
| CE | View CE declarations | |
| CSA File # | LR069014 | |
| RoHS Status | Yes (See CE Doc) | |
| EU REACH | View EU REACH document | |