

J808HLL Cut Sheet



Stahlin J series enclosure, NEMA 1/3R/4X/6P/12, 8 x 8 x 4in (HxWxD), wall mount, fiberglass reinforced polyester, gray, single-door, (1) twist-lock latch.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/J808HLL>

Technical Specifications

Brand	Stahlin	Integral Mounting Feet	No
Item	Enclosure	Integral Mounting Flange	Yes
Series	J	Dual Access	No
Subpanel	Purchase subpanel separately	Knockouts	No
Slope Top	No	Material	Fiberglass reinforced polyester
NEMA Rating	1/3R/4X/6P/12	Color	Gray
IP Rating	IP66	Cover Type	Single-door
Nominal Enclosure Dimensions	8 x 8 x 4in (HxWxD)	Hinge Type	Continuous hinge
Enclosure Height	9.56in	Number of Hinges Per Door	1
Enclosure Width	9.38in	Latch Type	(1) twist-lock latch
Enclosure Depth	4.87in	Padlockable	No
Mounting	Wall	Keylocking	No

Agency Approvals

UL Listed File #	E64358	E362920
UL Recognized File #	E333478	
UL Hazardous File #	None	
CE	View CE declarations	
CSA File #	LR069014	
RoHS Status	Yes (See CE Doc)	
EU REACH	View EU REACH document	