

J887PVC Cut Sheet



Stahlin NewSentry series enclosure, NEMA 1/2/3/4/4X/12/13, 8 x 8 x 7in (HxWxD), wall mount, PVC, gray, screw cover.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/J887PVC>

Technical Specifications

Brand	Stahlin
Item	Enclosure
Series	NewSentry
Slope Top	No
3-Piece Assembly	No
Vented	No
NEMA Rating	1/2/3/4/4X/12/13
Nominal Enclosure Dimensions	8 x 8 x 7in (HxWxD)
Enclosure Height	9.15in
Enclosure Width	9.15in
Enclosure Depth	7.65in
Mounting	Wall

Integral Mounting Feet	No
Integral Mounting Flange	No
Dual Access	No
Knockouts	No
Bottom Gland Plate	No
Material	PVC
Color	Gray
Cover Type	Screw cover
Shelf	No
Padlockable	No
Keylocking	No

Agency Approvals

UL Listed File #	E190960
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/J887PVC.pdf>
See store item page for other formats.