

JHL8 Cut Sheet



Edison drive fuse, JHL series, Class J, current-limiting, high speed, 8A, 600 VAC, ferrule. Package of 10. Feeder/branch, semiconductor protection applications.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/JHL8>

Technical Specifications

| | |
|-----------------------|--|
| Brand | Edison |
| Item | Drive fuse |
| Series | JHL |
| Fuse Class | Class J |
| Current-Limiting | Yes |
| Curve Characteristics | High speed |
| Amperage Rating | 8A |
| Voltage Rating | 600 VAC |
| Body Type | Ferrule |
| Size | 13/16x2-1/4in or 20.6x57.2mm |
| Quantity per Pack | 10 |
| Application | Feeder/branch, semiconductor protection applications |

Agency Approvals

| | |
|----------------------|--|
| UL Listed File # | E162363 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | 2322530 |
| RoHS Status | No |
| EU REACH | View EU REACH document |
| Other | None |