

# JM60100-1MW14-2 Cut Sheet



Bussmann modular power distribution fuse block, multi-wire, accepts J fuses, 100A, 600V, 2-pole, 1 line/4 load opening(s) per pole, box lug, panel mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/JM60100-1MW14-2>

## Technical Specifications

Brand	Bussmann	Openings Per Pole	1 line/4 load
Item	Power distribution fuse block	Line Side Conductor Size	14-1/0 AWG copper or aluminum
Modular	Yes	Load Side Conductor Size	(4) 14-4 AWG copper or (4) 8-4 AWG aluminum
Blown Fuse Indicator	No	Conductor Connection Type	Box lug
Multi-Wire	Yes	SCCR Rating	200kA SCCR
Accepts Fuse Class	J	Fuse Connection Type	Clip with reinforced spring
Amperage Rating	100A	Mounting	Panel
Voltage Rating	600V	Additional Information	Covers sold separately
Number of Poles	2		

## Agency Approvals

UL Listed File #	None
UL Recognized File #	E14853
UL Hazardous File #	None
CE	<a href="#">View CE declarations</a>
CSA File #	47235 - 6225-01
RoHS Status	No
EU REACH	<a href="#">View EU REACH document</a>
Other	None

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/JM60100-1MW14-2.pdf>  
See store item page for other formats.