

JM60100-1MW14-3 Cut Sheet



Bussmann modular power distribution fuse block, multi-wire, accepts J fuses, 100A, 600V, 3-pole, 1 line/4 load opening(s) per pole, box lug, panel mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/JM60100-1MW14-3>

Technical Specifications

| | | | |
|----------------------|-------------------------------|---------------------------|---------------------------------------------|
| Brand | Bussmann | Openings Per Pole | 1 line/4 load |
| Item | Power distribution fuse block | Line Side Conductor Size | 14-1/0 AWG copper or aluminum |
| Modular | Yes | Load Side Conductor Size | (4) 14-4 AWG copper or (4) 8-4 AWG aluminum |
| Blown Fuse Indicator | No | Conductor Connection Type | Box lug |
| Multi-Wire | Yes | SCCR Rating | 200kA SCCR |
| Accepts Fuse Class | J | Fuse Connection Type | Clip with reinforced spring |
| Amperage Rating | 100A | Mounting | Panel |
| Voltage Rating | 600V | Additional Information | Covers sold separately |
| Number of Poles | 3 | | |

Agency Approvals

| | |
|----------------------|----------------------------------------|
| UL Listed File # | None |
| UL Recognized File # | E14853 |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | 47235 - 6225-01 |
| RoHS Status | No |
| EU REACH | View EU REACH document |
| Other | None |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/JM60100-1MW14-3.pdf>
See store item page for other formats.