

# JM60200-1MW16-3 Cut Sheet



Bussmann modular power distribution fuse block, multi-wire, accepts J fuses, 200A, 600V, 3-pole, 1 line/6 load opening(s) per pole, box lug, panel mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/JM60200-1MW16-3>

## Technical Specifications

<b>Brand</b>	Bussmann
<b>Item</b>	Power distribution fuse block
<b>Modular</b>	Yes
<b>Blown Fuse Indicator</b>	No
<b>Multi-Wire</b>	Yes
<b>Accepts Fuse Class</b>	J
<b>Amperage Rating</b>	200A
<b>Voltage Rating</b>	600V
<b>Number of Poles</b>	3

<b>Openings Per Pole</b>	1 line/6 load
<b>Line Side Conductor Size</b>	6 AWG-250 MCM copper or aluminum
<b>Load Side Conductor Size</b>	(6) 14-4 AWG copper or (6) 8-4 AWG aluminum
<b>Conductor Connection Type</b>	Box lug
<b>SCCR Rating</b>	200kA SCCR
<b>Fuse Connection Type</b>	Clip with reinforced spring
<b>Mounting</b>	Panel
<b>Additional Information</b>	Covers sold separately

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	E14853
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	47235 - 6225-01
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>
<b>Other</b>	None

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/JM60200-1MW16-3.pdf>  
See store item page for other formats.