

JM60400-1MW16-3 Cut Sheet



Bussmann modular power distribution fuse block, multi-wire, accepts J fuses, 400A, 600V, 3-pole, 1 line/6 load opening(s) per pole, box lug, panel mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/JM60400-1MW16-3>

Technical Specifications

Brand	Bussmann	Openings Per Pole	1 line/6 load
Item	Power distribution fuse block	Line Side Conductor Size	4 AWG-600 MCM copper or aluminum
Modular	Yes	Load Side Conductor Size	(6) 14-2 AWG copper or (6) 8-2 AWG aluminum
Blown Fuse Indicator	No	Conductor Connection Type	Box lug
Multi-Wire	Yes	SCCR Rating	200kA SCCR
Accepts Fuse Class	J	Fuse Connection Type	Clip with reinforced spring
Amperage Rating	400A	Mounting	Panel
Voltage Rating	600V	Additional Information	Covers sold separately
Number of Poles	3		

Agency Approvals

UL Listed File #	None
UL Recognized File #	E14853
UL Hazardous File #	None
CE	View CE declarations
CSA File #	47235 - 6225-01
RoHS Status	No
EU REACH	View EU REACH document
Other	None

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/JM60400-1MW16-3.pdf>
See store item page for other formats.