

JM60600-1CR-3 Cut Sheet



Bussmann modular fuse block, accepts J fuses, 600A, 600V, 3-pole, 2 line/2 load opening(s) per pole, (2) 4 AWG-500 MCM copper or aluminum, box lug, panel mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/JM60600-1CR-3>

Technical Specifications

| | |
|----------------------------------|--------------------------------------|
| Brand | Bussmann |
| Item | Fuse block |
| Modular | Yes |
| Blown Fuse Indicator | No |
| Multi-Wire | No |
| Accepts Fuse Class | J |
| Amperage Rating | 600A |
| Voltage Rating | 600V |
| Number of Poles | 3 |
| Openings Per Pole | 2 line/2 load |
| Conductor Size | (2) 4 AWG-500 MCM copper or aluminum |
| Conductor Connection Type | Box lug |
| SCCR Rating | 200kA SCCR |
| Fuse Connection Type | Clip with reinforced spring |
| Mounting | Panel |
| Additional Information | Covers sold separately |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | E14853 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | 47235 - 6225-01 |
| RoHS Status | No |
| EU REACH | View EU REACH document |
| Other | None |