

JW1816HPL Cut Sheet



Stahlin JW series enclosure, NEMA 1/3R/4X/6P/12, 18 x 16 x 8in (HxWxD), wall mount, fiberglass reinforced polyester, gray, single-door, (2) quick-release latches, padlock hasp and staple, SAR acrylic window.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/JW1816HPL>

Technical Specifications

| | | | |
|-------------------------------------|------------------------------|----------------------------------|---------------------------------|
| Brand | Stahlin | Integral Mounting Flange | Yes |
| Item | Enclosure | Dual Access | No |
| Series | JW | Knockouts | No |
| Subpanel | Purchase subpanel separately | Bottom Gland Plate | No |
| Slope Top | No | Material | Fiberglass reinforced polyester |
| 3-Piece Assembly | No | Color | Gray |
| Vented | No | Cover Type | Single-door |
| NEMA Rating | 1/3R/4X/6P/12 | Hinge Type | Continuous hinge |
| IP Rating | IP66 | Number of Hinges Per Door | 1 |
| Nominal Enclosure Dimensions | 18 x 16 x 8in (HxWxD) | Latch Type | (2) quick-release latches |
| Enclosure Height | 19.62in | Padlock Attachment Type | Padlock hasp and staple |
| Enclosure Width | 17.61in | Shelf | No |
| Enclosure Depth | 8.82in | Window Material | SAR acrylic |
| Mounting | Wall | Padlockable | Yes |
| Integral Mounting Feet | No | Keylocking | No |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | E64358 |
| UL Recognized File # | E333478 |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | LR069014 |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/JW1816HPL.pdf>
See store item page for other formats.